



Ko te ahua he whakaahua.
Tirohia nga whakaritenga mo nga taipitopito hua.

HV2301FG-G

Tau Wae: **HV2301FG-G**
 Whakaahuatanga Hua: IC ULTRASOUND SWITCH 1:1 48LQFP
 RoHs Tūnga: Whakahaerehia te kore utu / RoHS
 Ngā Rauemi:

Kaihanga / Waitohu: N/A
 Tuhinga mai i: Hong Kong
 Te Ara Tuhi: DHL/Fedex/TNT/UPS/EMS

TUKUNA HE UIUI >

Taipitopito hua

Tau Wae	HV2301FG-G	Kaihanga	N/A
Whakaahuatanga	IC ULTRASOUND SWITCH 1:1 48LQFP	Whakahaere Toko Whakahaere / RoHS Tūnga	Whakahaerehia te kore utu / RoHS
Pepa Raraunga			
Ngaohihi - Whakaaetanga, Kotahi (V +)	40 V ~ 200 V	Ngaohihi - Whakaaetanga, Tino (V ±)	±40 V ~ 160 V
Whakawhitihia te Kotahitanga	SPST	Pūrere Pūrere Whakarato	48-LQFP (7x7)
Raupapa	-	Packaging	Tray
Paa / Case	48-LQFP	Tae Mahi	0°C ~ 70°C (TA)
Whakaoho-a-Whenua (Max)	38 Ohm	Te maha o nga pouaka	8
Mahahiko Maha / Whakawanui Whakawhiti	1:1	Taumata Whakaaro Moe (MSL)	3 (168 Hours)
Te Tae Kaituku Taeke	5 Weeks	Whakahaere Toko Whakahaere / RoHS Tūnga	Lead free / RoHS Compliant
Ngā āhuatanga	-	Whakaahuatanga Taipitopito	Ultrasound Switch IC 8 Channel 48-LQFP (7x7)
Tau Wae Tuakiri	HV2301	Nga tono	Ultrasound
-3db Whaiwhata	50MHz		

Hua e Hono ana

<p>HV2225Y822KXHATHV Kaihanga: Electro-Films (EFI) / Vishay Whakaahuatanga: CAP CER 8200PF 3KV X7R 2225 Tikiake: HV2225Y822KXHATHV.pdf</p> <p><input type="button" value="RFQ"/></p>	<p>HV230G1-G Kaihanga: N/A Whakaahuatanga: IC ULTRASOUND SWITCH 1:1 28LLGA</p> <p><input type="button" value="RFQ"/></p>
<p>HV2225Y822MXHATHV Kaihanga: Electro-Films (EFI) / Vishay Whakaahuatanga: CAP CER 8200PF 3KV X7R 2225 Tikiake: HV2225Y822MXHATHV.pdf</p> <p><input type="button" value="RFQ"/></p>	<p>HV2301FG-G-M931 Kaihanga: N/A Whakaahuatanga: IC ULTRASOUND SWITCH 1:1 48LQFP</p> <p><input type="button" value="RFQ"/></p>
<p>HV2321FG-G Kaihanga: N/A Whakaahuatanga: IC ULTRASOUND SWITCH 1:1 48LQFP</p> <p><input type="button" value="RFQ"/></p>	<p>HV231-10A Kaihanga: Amprobe Whakaahuatanga: HV PROBE 10 MEGOHM Tikiake: HV231-10A.pdf</p> <p><input type="button" value="RFQ"/></p>
<p>HV2301PJ-G Kaihanga: N/A Whakaahuatanga: IC ULTRASOUND SWITCH 1:1 28PLCC</p> <p><input type="button" value="RFQ"/></p>	<p>HV2225Y822JXHATHV Kaihanga: Electro-Films (EFI) / Vishay Whakaahuatanga: CAP CER 8200PF 3KV X7R 2225 Tikiake: HV2225Y822JXHATHV.pdf</p> <p><input type="button" value="RFQ"/></p>
<p>HV2230800000G Kaihanga: Anytek (Amphenol Anytek) Whakaahuatanga: 381 TB SPRING CLAMP 90D Tikiake: HV2230800000G.pdf</p> <p><input type="button" value="RFQ"/></p>	<p>HV230GA-G Kaihanga: N/A Whakaahuatanga: IC ANALOG SWITCH 8CH 26FBGA</p> <p><input type="button" value="RFQ"/></p>
<p>HV2225Y821MXVATHV Kaihanga: Electro-Films (EFI) / Vishay Whakaahuatanga: CAP CER 820PF 4KV X7R 2225 Tikiake: HV2225Y821MXVATHV.pdf</p> <p><input type="button" value="RFQ"/></p>	<p>HV2225Y821MXMATHV Kaihanga: Electro-Films (EFI) / Vishay Whakaahuatanga: CAP CER 820PF 5KV X7R 2225 Tikiake: HV2225Y821MXMATHV.pdf</p> <p><input type="button" value="RFQ"/></p>

Nga tohu e pa ana

HV2301FG-G	HV2301FG-G Kaitoha	HV2301FG-G Kaiwhakarato
HV2301FG-G Utu	HV2301FG-G Nga Whakaahua	HV2301FG-G Whakaahua
Pukaiti PDF HV2301FG-G PDF	HV2301FG-G Tangohia te Pukaiti	Pukaiti HV2301FG-G
HV2301FG-G Stock	Hokona HV2301FG-G	Hokona HV2301FG-G
HV2301FG-G	Kaiwhakarato	Kaitoha